



Representative

Catalog Number: 314
Product ID: 7TAA106030R0017
UPC Number: 78621000314
EAN Number: 05415022259100
Status: A

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 2-1/2 Inch, Knockout Size 2-1/2 Inch, Cable Range 2.812 to 3.062 Inch, Malleable Iron with Zinc Plating

- For use with Armored Cable and Flexible Metal Conduit

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Brand Name	T&B
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Easy to Install with Double Grip Saddle, Connectors are Completely Salvageable
Application	To Connect and Effectively Bond Metal-Clad Cables, Armored Cable, and Flexible Metal Conduit to a Box or Enclosure
Standard	UL E23018, CSA
Size	2 1/2 Inch
Conductor Range	2.812 to 3.062 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	No

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated
Thread length	71.43mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	1
Inner Dimensions (inches)	6x4x4
Outer Quantity	5
Outer Dimensions (inches)	21.6x5.3x7.2
Weight Uom	273.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------

