



Representative

Catalog Number: 323
Product ID: 7TAA106020R0014
UPC Number: 78621000323
EAN Number: 05414363141006
Status: A

Metal-Clad and Armored Cable Fitting, 90 Degree Bend, Trade Size 1/2 Inch, Knockout Size 1/2 Inch, Cable Range 0.670 to 0.920 Inch, Malleable Iron with Zinc Plating

- Throat is long enough to install in cast housing knockouts.
- To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	The Angle Clip Gives Secure Mechanical Grip that Tightens Under Tension or Vibration
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA 2884
Size	1/2 Inch
Conductor Range	0.670 to 0.920 Inch
Material	Steel
Finish	Electro Zinc Plated
Color	Metallic

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated
Thread length	30.95mm

Packaging

Inner Quantity	25
Inner Dimensions (inches)	4x5x8
Outer Quantity	100
Outer Dimensions (inches)	10.7x8.9x8.8
Weight Uom	21.63 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

Header

3D Model	Available on Website
----------	----------------------

