



Actual



Representative

**Catalog Number:** 3302-C  
**Product ID:** 7TAA106100R0001  
**UPC Number:** 78621036087  
**Status:** A

1/2 Inch Non-Metallic Sheathed Cable Two Screw Connector, For NMSC 14/3, 12/3, 10/2 or 10/3, For Multiple (2) NM Cables 14/2 or 12/2, For Flexible Cord Cable Openings (.250 Inch to .650 Inch), For Multiple Flexible Cords (.250 Inch Combined Diameter Minimum) For Service Entrance Cables (.464 Inch X .235 Inch or Larger)

### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Nonmetallic Sheathed Cable Fittings
Special Features	Rounded Cable Grip and Smooth Bushing Protect The Cable Sheath and Wire Insulation. Since Saddle is Threaded, Screws Do Not Travel or Extend Beyond The Connector Body As It is Clamped to The Cable. An Extra Lip on The Saddle Closes The Unused Part of The Connector Opening.
Application	To Connect Nonmetallic Sheathed Cable and Flexible Cord to a Box or an Enclosure.
Standard	CSA, UL
Size	1/2 Inch
Material	Steel - Non Insulated
Finish	Zinc Plated
Color	Metallic

### European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Other
Thread connection size	Other

### Packaging

Inner Quantity	100
Inner Dimensions (inches)	4x5x8
Outer Quantity	500
Outer Dimensions (inches)	21.1x5.8x8.6
Weight Uom	5.75 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website