



**Catalog Number:** 3303SL  
**Product ID:** 7TAA106090R0004  
**UPC Number:** 78621093392  
**Status:** A

3/4 Inch Non-Metallic Sheathed Cable - Two Screw Connector with Slotted Head Screw, For Non-Metallic Sheathed Cables 8/2, 8/3 or 6/2, For Multiple (2) NM Cables 12/2 or 14/3, For Flexible Cords Cable Opening .530 Inch to .835 Inch, For Multiple Flexible Cords (.530 Combined Diameter Minimum) (2) 18/3 Minimum, For Service Entrance Cables Minimum Opening .395 Inch X .622 Inch

#### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Non-Metallic Sheathed Cable Conduit Fittings
Special Features	Rounded Cable Grip and Smooth Bushing Protect The Cable Sheath and Wire Insulation, Since Saddle is Threaded, Screws Do Not Travel or Extend Beyond The Connector Body As It is Clamped to The Cable, An Extra Lip on The Saddle Closes The Unused Part of The Connector Opening.
Size	3/4 Inch
Material	Steel
Finish	Electro Zinc Plated
Color	Metallic

#### European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Other
Thread connection size	Other

#### Packaging

Inner Quantity	50
Inner Dimensions (inches)	8.25x5.25x4.25
Outer Quantity	250
Outer Dimensions (inches)	21x5.5x8.62
Weight Uom	11.19 lbs. per 100