



Actual



Representative

Catalog Number: 3305M
Product ID: 7TAA106090R0005
UPC Number: 78621080555
EAN Number: 05414363141082
Status: A

Sheathed Cable Fitting, Straight, Knockout Size 1-1/4 Inch, Nylon Insulated, Two Screw Connector, Malleable Iron with Zinc Plating

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Non-Metallic Sheathed Cable Conduit Fittings
Special Features	Rounded Cable Grip and Smooth Bushing Protect The Cable Sheath and Wire Insulation. Since Saddle is Threaded, Screws Do Not Travel or Extend Beyond The Connector Body As It is Clamped to The Cable. An Extra Lip on The Saddle Closes The Unused Part of The Connector Opening.
Application	To Connect Non-Metallic Sheathed Cable and Flexible Cord to a Box or an Enclosure.
Standard	UL E23013, CSA 2884
Size	1-1/4 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated

Packaging

Inner Quantity	5
Inner Dimensions (inches)	4x4x3
Outer Quantity	25
Outer Dimensions (inches)	16x5.2x6
Weight Uom	27.38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

Header

3D Model	Available on Website
----------	----------------------

