



Actual



Representative

**Catalog Number:** 3310  
**Product ID:** 7TAA106090R0008  
**UPC Number:** 78621003310  
**Status:** A

Sheathed Cable Fitting, Straight, Knockout Size 3-1/2 Inch, Two Screw Connector, Malleable Iron with Zinc Plating

**North American Specifications (UNSPSC)**

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Non-Metallic Sheathed Cable Conduit Fittings
Special Features	Rounded Cable Grip and Smooth Bushing Protect The Cable Sheath and Wire Insulation. Since Saddle is Threaded, Screws Do Not Travel or Extend Beyond The Connector Body As It is Clamped to The Cable. An Extra Lip on The Saddle Closes The Unused Part of The Connector Opening.
Application	To Connect Non-Metallic Sheathed Cable and Flexible Cord to a Box or an Enclosure.
Size	3-1/12 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	No

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated

**Packaging**

Outer Quantity	1
Outer Dimensions (inches)	6.75x4.5x4.5
Weight Uom	2.88 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

**Header**

3D Model	Available on Website
----------	----------------------