



Representative

Catalog Number: 331
Product ID: 7TAA106030R0027
UPC Number: 78621000331
Status: A

Metal-Clad and Armored Cable Fitting, 90 Degree Bend, Trade Size 3 Inch, Knockout Size 3 Inch, Cable Range 3.312 to 3.562 Inch, Malleable Iron with Zinc Plating

- Throat is long enough to install in cast housing knockouts.
- To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	The Angle Clip Gives Secure Mechanical Grip that Tightens Under Tension or Vibration
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA 2884
Size	3 Inch
Conductor Range	3.312 to 3.562 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated

Packaging

Outer Quantity	1
Outer Dimensions (inches)	10.7x5.5x7
Weight Uom	780 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------