



Actual



Representative

Catalog Number: 3726
Product ID: 7TAD012090R0004
UPC Number: 78621003726
EAN Number: 05414363101949
Status: A

2 Inch Malleable Iron Type A Straight Liquidtight Connector With Insulated Throat and Sealing Ring With Iron Retainer

- Steel or malleable iron construction with nylon-insulated throat
- Santoprene sealing gasket includes Type 316 stainless steel retaining ring.
- NPT hub threads seal in female threads.
- Offers high mechanical pull-out strength.
- Supplied with sealing ring and steel locknut.
- Available in straight, 45 degree and 90 degree in hub sizes from 3/8 inch to 2 inch.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-Straight
Application	Provides a positive seal against water, oil and dust.
Standard	UL E23018
Size	2 Inch
Material	Malleable Iron

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
One-piece	N
Material screw gland	Metal
Material sealing	Other
Colour	Other

Packaging

Inner Quantity	1
Inner Dimensions (inches)	6x4x4
Outer Quantity	5
Outer Dimensions (inches)	21.4x5.3x7.2
Weight Uom	228 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA00886-TB2

Header

3D Model	Available on Website
----------	----------------------

