



Actual



Representative

Catalog Number: 3731-TB
Product ID: 7TAD012090R0005
UPC Number: 78621003731
EAN Number: 05414363101963
Status: A

1/2 Inch 45 Degree Iron Type A Liquidtight Connector With Insulated Throat and Iron Retainer

- Steel or malleable iron construction with nylon-insulated throat
- Santoprene sealing gasket includes Type 316 stainless steel retaining ring.
- NPT hub threads seal in female threads.
- Offers high mechanical pull-out strength.
- Supplied with sealing ring and steel locknut.
- Available in straight, 45 degree and 90 degree in hub sizes from 3/8 inch to 2 inch.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-45 Degree
Application	Provides a positive seal against water, oil and dust.
Standard	UL E23018
Size	1/2 Inch
Material	Steel

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1/2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
One-piece	N
Material screw gland	Metal
Material sealing	Other
Colour	Other

Packaging

Inner Quantity	25
Inner Dimensions (inches)	9.5x6.3x3.2
Outer Quantity	50
Outer Dimensions (inches)	9.9x7.6x10.4
Weight Uom	39.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000107
Instruction Sheet	TA02932-TB2

Header

3D Model	Available on Website
----------	----------------------

