



Actual



Representative

Catalog Number: 3736
Product ID: 7TAD012520R0005
UPC Number: 78621003736
EAN Number: 05414363190615
Status: A

2 Inch Malleable Iron Type A to 45 Degree Liquidtight Connector With Insulated Throat and Sealing Ring With Iron Retainer

- Steel or malleable iron construction with nylon-insulated throat
- Santoprene sealing gasket includes Type 316 stainless steel retaining ring.
- NPT hub threads seal in female threads.
- Offers high mechanical pull-out strength.
- Supplied with sealing ring and steel locknut.
- Available in straight, 45 degree and 90 degree in hub sizes from 3/8 inch to 2 inch.
- Provides a positive seal against water, oil and dust.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Liquidtight Flexible Metal Conduit Fittings
Standard	UL E23018
Size	2 Inch
Material	Malleable Iron
Color	Silver

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
One-piece	N
Material screw gland	Metal
Material sealing	Other
Colour	Other

Packaging

Inner Quantity	1
Inner Dimensions (inches)	6x4x4
Outer Quantity	5
Outer Dimensions (inches)	6.9x21.9x5.3
Weight Uom	2.7 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Instruction Sheet	TA00886-TB2

Header

3D Model	Available on Website
----------	----------------------

