



Representative

**Catalog Number:** 3740  
**Product ID:** 7TAD012520R0006  
**UPC Number:** 78621003740  
**EAN Number:** 05414363102014  
**Status:** A

3/8 Inch Iron Type A to 90 Degree Liquidtight Connector With Insulated Throat and Sealing Ring With Iron Retainer

- Steel or malleable iron construction with nylon-insulated throat
- Santoprene sealing gasket includes Type 316 stainless steel retaining ring.
- NPT hub threads seal in female threads.
- Offers high mechanical pull-out strength.
- Supplied with sealing ring and steel locknut.
- Available in straight, 45 degree and 90 degree in hub sizes from 3/8 inch to 2 inch.
- Provides a positive seal against water, oil and dust.

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Liquidtight Flexible Metal Conduit Fittings
Standard	UL E23018
Size	3/8 Inch
Material	Steel
Color	Silver

### European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	3/8 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	15mm
One-piece	N
Material screw gland	Metal
Colour	Other

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	8.1x4.19x5.1
Outer Quantity	50
Outer Dimensions (inches)	10.8x8.39x4.5
Weight Uom	27.19 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000108
Catalog Page	Available on Website
Instruction Sheet	TA02932-TB2

### Header

3D Model	Available on Website
----------	----------------------

