



Actual



Representative

**Catalog Number:** 4234  
**Product ID:** 7TAD013170R0003  
**UPC Number:** 78621004234  
**Status:** A

1-1/2 Inch Short Elbow, Malleable Iron for Use with EMT Conduit

- Shoulders on body of 1/2 inch size are hex-shaped to provide positive holding for standard installation tools.

### North American Specifications (UNSPSC)

UNSPSC	39131717 Electrical conduit elbow
IGCC	5746 Electrical conduit elbow
Type	Rigid/IMC Conduit Fittings
Application	To Connect and Effectively Bond Threaded Rigid Metal Conduit/Intermediate Metal Conduit to a Box or Enclosure, or to Couple Ends of Threaded Conduit
Standard	UL E16592, CSA
Material	Malleable Iron
Trade Size	1-1/2 in

### European Specifications (ETIM)

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Other
Colour	Natural colour
Model	Rigid
Angle of bow	90°

### Packaging

Inner Quantity	2
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	10
Outer Dimensions (inches)	24.2x6.2x3.5
Weight Uom	140 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

### Header

3D Model	Available on Website
----------	----------------------