



Catalog Number: 463
Product ID: 7TAD013720R0009
UPC Number: 78621000463
Status: A



Representative

1-1/4 Inch Bushed Elbow, Malleable Iron for Use with Rigid/IMC Conduit

North American Specifications (UNSPSC)

UNSPSC	39131717 Electrical conduit elbow
IGCC	5746 Electrical conduit elbow
Type	Rigid/IMC Conduit Fittings
Special Features	The Non-Insulated Elbow Has Smoothly Rounded Shoulders to Protect Conductor Insulation.
Application	To Connect and Effectively Bond Threaded Rigid Metal Conduit/Intermediate Metal Conduit to a Box or Enclosure, or to Couple Ends of Threaded Conduit
Standard	UL E23018, CSA
Material	Malleable Iron
Trade Size	1-1/4 in

European Specifications (ETIM)

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Other
Colour	Natural colour
Model	Rigid
Angle of bow	90°

Packaging

Inner Quantity	5
Inner Dimensions (inches)	8x5x4
Outer Quantity	10
Outer Dimensions (inches)	8.7x8.6x5.8
Weight Uom	1.24 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------