



Actual



Representative

Catalog Number: 4960
Product ID: 7TBD105180R0003
UPC Number: 78621004960
EAN Number: 05414363102076
Status: A

Liquidtight Strain Relief Connector, 1/2 Inch, 90 Degree Bend, Cord Range 0.125 to 0.375 Inch, Throat Diameter 19/32 Inch, Malleable Iron Body, Steel Gland, Plastic Grip, Santropene Bushing

- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.
- Suitable for Ordinary, Wet or Dry locations.
- Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord Connectors-90 Degree
Special Features	Extended Range with Superior Strain Relief
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead
Standard	UL E13938, CSA 52391
Size	1/2 Inch
Conductor Range	0.125 to 0.375 Inch
Material	Malleable Iron
Color	Metallic
Environmental Conditions	Ordinary, Wet, or Dry Locations

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Suitable for cable diameter	3.175-9.525mm
Material	Metal
Material quality	Other
Colour	Natural colour
Model	90°-elbow

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x5x4
Outer Quantity	50
Outer Dimensions (inches)	8.9x5.7x6.8
Weight Uom	24.88 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

Header

3D Model	Available on Website
----------	----------------------

