



Actual



Representative

**Catalog Number:** 4960AL  
**Product ID:** 7TBD105100R0004  
**UPC Number:** 78621079758  
**EAN Number:** 05415022258998  
**Status:** Active

Liquidtight Strain Relief Connector, 1/2 Inch, 90 Degree Bend, Cord Range 0.125 to 0.375 Inch, Throat Diameter 19/32 Inch, Aluminum Body, Glandnut, and Grip, Rubber Bushing

- Extended range with superior strain relief.
- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.
- Provide a means for passing a cord cable into an enclosure through a bulkhead
- Suitable for Ordinary, Wet or Dry locations.
- Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Cord Connectors-90 Degree
Special Features	Extended Range with Superior Strain Relief
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead
Standard	UL E13938, CSA 52391
Size	1/2 Inch
Conductor Range	0.125 to 0.375 Inch
Material	Aluminum
Color	Metallic
Environmental Conditions	Ordinary, Wet, or Dry Locations

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	15.875mm
Suitable for cable diameter	3.175-9.525mm
Material	Metal
Material quality	Aluminium
Colour	Natural colour
Model	90°-elbow

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x5x4
Outer Quantity	50
Outer Dimensions (inches)	10.9x8.8x5.1
Weight Uom	11 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

### Header

3D Model	Available on Website
----------	----------------------

