



Actual



Representative

Catalog Number: 4972AL
Product ID: 7TBD105110R0023
UPC Number: 78621079763
EAN Number: 05415022495843
Status: A

Liquidtight Strain Relief Connector, 3/4 Inch, 90 Degree Bend, Cord Range 0.500 to 0.750 Inch, Throat Diameter 25/32 Inch, Aluminum Body, Glandnut, and Grip, Rubber Bushing

- Extended range with superior strain relief.
- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.
- Provide a means for passing a cord cable into an enclosure through a bulkhead
- Suitable for Ordinary, Wet or Dry locations.
- Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord Connectors-90 Degree
Special Features	Extended Range with Superior Strain Relief
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead
Standard	UL E13938, CSA 52391
Size	3/4 Inch
Conductor Range	0.500 to 0.750 Inch
Material	Aluminum
Color	Metallic
Environmental Conditions	Ordinary, Wet, or Dry Locations

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	17.46mm
Suitable for cable diameter	12.7-19.05mm
Material	Metal
Material quality	Aluminium
Colour	Natural colour
Model	90°-elbow

Packaging

Inner Quantity	10
Inner Dimensions (inches)	6x4x4
Outer Quantity	20
Outer Dimensions (inches)	xx
Weight Uom	30.38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000044
Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Support/Tools	Available on Website

Header

3D Model

Available on Website