



Actual



Representative

Project: Lower Lock Wall Instrument Conduits
Location: KY Dam

Collier

Catalog Number: 5234-TB
Product ID: 7TAD012100R0003
UPC Number: 78621005234
EAN Number: 05414363142737
Status: A

1 Inch Straight Steel Liquidtight Connector, Non-insulated

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-Straight
Application	Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.
Standard	UL E23018, CSA
Size	1 Inch
Material	Steel
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Surface protection	Zinc coated
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	10
Inner Dimensions (inches)	8x5x4
Outer Quantity	50
Outer Dimensions (inches)	20.81x5.18x8.12
Weight Uom	37.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001535
--------------------------------	------------



Instruction Sheet

TA00210-TB2

Support/Tools

Available on Website

Header

3D Model

Available on Website