



Actual



Representative

Location: Houston

irby

3520 s.sam houston pkwy e
suite 200

Catalog Number: 5236
Product ID: 7TAD012150R0000
UPC Number: 78621005236
EAN Number: 05414363142768
Status: A

Liquidtight Conduit Fitting, Straight 1-1/2 Inch, Non-Insulated Malleable Iron

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-Straight
Application	Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.
Standard	UL E23018, CSA
Size	1-1/2 Inch
Material	Steel
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	2
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	10
Outer Dimensions (inches)	21.62x6.12x6.62
Weight Uom	96.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
--------------------------------	-----------



Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Catalog US	Available on Website

Header	
3D Model	Available on Website