



Representative

Catalog Number: 5236AL
Product ID: 7TAD012250R0002
UPC Number: 78621080251
EAN Number: 05414363142775
Status: A

1-1/2 Inch Aluminum Liquidtight Connector, Straight, Non-insulated

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-Straight
Application	High-quality, corrosion-resistant, liquidtight termination for LTA flexible aluminum conduit.
Standard	UL E23018, CSA
Size	1-1/2 Inch
Material	Aluminum
Finish	Zinc Plating/Clear Chromate

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Surface protection	Zinc coated
Thread length	20.63mm
Total length	68.26mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	2
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	10
Outer Dimensions (inches)	4.1x23.9x5.5
Weight Uom	38.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000118
Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------

