



Representative

Project: TC Energy - Shellburn

Catalog Number: 5236GR
Product ID: 7TAD012310R0006
UPC Number: 78621089609
Status: A

1-1/2 Inch Steel External Bonding Liquidtight Connector, Non-insulated, Straight

- Ability to install quickly with low torque effort

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-Straight
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	1-1/2 Inch
Material	Steel
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	2
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	10
Outer Dimensions (inches)	4.19x24.1x5.8
Weight Uom	125 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Support/Tools	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------

