



Representative

Catalog Number: 5239GR
Product ID: 7TAD012300R0001
UPC Number: 78621089612
Status: A

3 Inch External Bonding Liquidtight, Flexible Metal Conduit Connector, Straight, With Copper Lug for #2 to 4/0 Ground Wire, for Use In Wet Locations, Non-insulated

- Ability to install quickly with low torque effort

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-Straight
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	3 Inch
Material	Steel
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Outer Quantity	1
Outer Dimensions (inches)	6.9x5.3x5.7
Weight Uom	525 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Catalog Page	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------