



Representative

**Catalog Number:** 5243GR  
**Product ID:** 7TAD012310R0010  
**UPC Number:** 78621089989  
**Status:** A

3/4 Inch 45 Degree Malleable Iron External Bonding Liquidtight Connector, Non-insulated

- Ability to install quickly with low torque effort

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-45 degree
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	3/4 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	6x5x4
Outer Quantity	50
Outer Dimensions (inches)	5.2x26.7x6.9
Weight Uom	40.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Catalog Page	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

### Header

3D Model	Available on Website
----------	----------------------