



Representative

Catalog Number: 5250GR
Product ID: 7TAD012420R0017
UPC Number: 78621089618
Status: A

4 Inch 45 Degree Malleable Iron External Bonding Liquidtight Connector, Non-insulated

- Ability to install quickly with low torque effort

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-45 Degree
Application	To Positively Bond Conduit to Box or Enclosure
Standard	UL E3060, CSA
Size	4 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	4 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other

Packaging

Outer Quantity	1
Outer Dimensions (inches)	10.1x7x8.6
Weight Uom	12.2 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Support/Tools	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------