



Actual



Representative

Catalog Number: 5251
Product ID: 7TAD012140R0004
UPC Number: 78621005251
EAN Number: 05415022257670
Status: A

Liquidtight Conduit Fitting, 90 Degree 3/8 Inch, Non-Insulated Malleable Iron

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

North American Specifications (UNSPSC)

| | |
|-------------|---|
| UNSPSC | 39121420 Liquid tight connectors |
| IGCC | 4585 Liquid tight connectors |
| Type | Connectors-90 Degree |
| Application | Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture. |
| Standard | UL E23018, CSA |
| Size | 3/8 Inch |
| Material | Malleable Iron |
| Finish | Electro Zinc Plated/Chromate Coating |

European Specifications (ETIM)

| | |
|---|--|
| ETIM | EC001180 Screw connection for protective metallic hose |
| Nominal size in inch | 3/8 inch |
| Model | 90°-elbow |
| Revolving thread | N |
| Construction type | External thread |
| Connection type screw connection to housing | Thread |
| Thread type | NPT |
| Thread connection size | Other |
| One-piece | N |
| Material housing | Other |
| Surface protection | Zinc coated |
| Approved in combination with protective conduit CSA | Y |
| Approved in combination with protective conduit UL | Y |

Packaging

| | |
|---------------------------|-----------------|
| Inner Quantity | 25 |
| Inner Dimensions (inches) | 6x5x4 |
| Outer Quantity | 50 |
| Outer Dimensions (inches) | 8.51x5.31x6.31 |
| Weight Uom | 21 lbs. per 100 |

Documents / Support Tools

| | |
|--------------------------------|----------------------|
| Technical Drawing / Data Sheet | TDS000122 |
| Catalog Page | Available on Website |
| Instruction Sheet | TA00210-TB2 |
| Support/Tools | Available on Website |
| Catalog US | Available on Website |

Header

| | |
|----------|----------------------|
| 3D Model | Available on Website |
|----------|----------------------|

