



Representative

Catalog Number: 5253AL-SG
Product ID: 7TAD012420R0020
UPC Number: 78620992897
Status: A

3/4 Inch 90 Degree Aluminum Liquidtight Connector With Sealing Gasket

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-90 Degree
Application	High-Quality, Corrosion-Resistant, Liquidtight Termination for LTA Flexible Aluminum Conduit.
Standard	UL E23018
Size	3/4 Inch
Material	Aluminum
Finish	Zinc Plating/Clear Chromate

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other

Packaging

Inner Quantity	10
Inner Dimensions (inches)	6.25x4.75x4.25
Outer Quantity	50
Outer Dimensions (inches)	21.62x5.12x6.62
Weight Uom	16.5 lbs. per 100

Documents / Support Tools

Instruction Sheet	TA00210-TB2
-------------------	-------------