



Representative

**Catalog Number:** 5254GR  
**Product ID:** 7TAD012310R0019  
**UPC Number:** 78621089995  
**Status:** A

1 Inch 90 Degree Malleable Iron External Bonding Liquidtight Connector, Non-insulated

- Ability to install quickly with low torque effort

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-90 degree
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	1 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

#### Packaging

Inner Quantity	5
Inner Dimensions (inches)	6.2x4.19x4.6
Outer Quantity	25
Outer Dimensions (inches)	6.9x5.1x22
Weight Uom	71 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Support/Tools	Available on Website
Catalog US	Available on Website

#### Header

3D Model	Available on Website
----------	----------------------