



Representative

Catalog Number: 5254GRX
Product ID: 7TAD012420R0023
UPC Number: 78621075943
Status: A

1 Inch 90 Degree Malleable Iron External Bonding Liquidtight Connector With Lay-in-lug, Non-insulated

- Ability to install quickly with low torque effort

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-90 degree
Application	To positively bond conduit to box or enclosure
Standard	UL E3060
Size	1 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	5
Inner Dimensions (inches)	6x4x4
Outer Quantity	25
Outer Dimensions (inches)	21.5x5.25x6.75
Weight Uom	68 lbs. per 100