



Actual



Representative

Catalog Number: 5255
Product ID: 7TAD012170R0003
UPC Number: 78621005255
EAN Number: 05414363142904
Status: A

Liquidtight Conduit Fitting, 90 Degree 1-1/4 Inch, Non-Insulated Malleable Iron

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-90 Degree
Application	Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.
Standard	UL E23018, CSA
Size	1-1/4 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	5
Inner Dimensions (inches)	9.5x6.5x4.5
Outer Quantity	25
Outer Dimensions (inches)	23.94x6.81x9.81
Weight Uom	1.13 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
Catalog Page	Available on Website
Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------

