



Catalog Number: 5255AL
Product ID: 7TAD012250R0005
UPC Number: 78621080257
Status: A

1-1/4 Inch 90 Degree Aluminum Liquidtight Connector, Non-insulated



Actual



Representative

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-90 Degree
Application	High-quality, corrosion-resistant, liquidtight termination for LTA flexible aluminum conduit.
Standard	UL E23018, CSA
Size	1-1/4 Inch
Material	Aluminum
Finish	Zinc Plating/Clear Chromate

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Surface protection	Zinc coated
Thread length	20.63mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	5
Inner Dimensions (inches)	8x5x4
Outer Quantity	25
Outer Dimensions (inches)	26.7x8.39x4.5
Weight Uom	50.38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000118
Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------

