



Actual



Representative

**Catalog Number:** 5256  
**Product ID:** 7TAD012170R0004  
**UPC Number:** 78621005256  
**EAN Number:** 05414363142911  
**Status:** A

Liquidtight Conduit Fitting, 90 Degree 1-1/2 Inch, Non-Insulated Malleable Iron

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-90 Degree
Application	Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.
Standard	UL E23018, CSA
Size	1-1/2 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/2 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

### Packaging

Inner Quantity	2
Inner Dimensions (inches)	8x5x4
Outer Quantity	10
Outer Dimensions (inches)	20.81x5.19x8.13
Weight Uom	155 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
Catalog Page	Available on Website
Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Catalog US	Available on Website

### Header

3D Model	Available on Website
----------	----------------------

