



Representative

Catalog Number: 5330
Product ID: 7TAD012470R0005
UPC Number: 78621005330
EAN Number: 05414363099963
Status: A

5/16 Inch Straight Steel Insulated Liquidtight Connector

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-Straight
Application	Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.
Size	5/16 Inch
Material	Steel
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	5/16 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Thread length	11.90mm
Total length	34.92mm
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	N

Packaging

Inner Quantity	25
Inner Dimensions (inches)	4x4x3
Outer Quantity	100
Outer Dimensions (inches)	8.7x7.1x5.1
Weight Uom	10.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
Catalog Page	Available on Website
Instruction Sheet	TA00210-TB2

Header

3D Model	Available on Website
----------	----------------------

