



Representative

Catalog Number: 5331
Product ID: 7TAD012100R0004
UPC Number: 78621005331
EAN Number: 05414363075622
Status: A

3/8 Inch Straight Steel Insulated Liquidtight Connector

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-Straight
Application	Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.
Standard	UL E23018, CSA
Size	3/8 Inch
Material	Steel
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/8 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x4.5x4
Outer Quantity	100
Outer Dimensions (inches)	9.56x8.63x6.31
Weight Uom	12.63 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------

