



**Catalog Number:** 5335090  
**Product ID:** 7TAD012980R0098  
**UPC Number:** 78621085596  
**Status:** A

3-1/2 Inch Liquidtight Flexible Metal Conduit Connector, 90 Degree Angle, Insulated, Safe to edge Ground Cone In Knockout Applications Use Sealing Ring 5269, Electro Zinc Plated to Chrome Coated, 1 Piece

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Liquidtight Fittings
Application	Provides a positive seal against oil, liquids, moisture and dust.
Size	3-1/2 Inch
Finish	Chromate

#### European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	3 1/2 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	29.97mm
Material screw gland	Metal

#### Packaging

Outer Quantity	1
Outer Dimensions (inches)	12.62x10.5x8.37
Weight Uom	1877.3 lbs. per 100