



Actual



Representative

**Catalog Number:** 5336-HT  
**Product ID:** 7TAD012420R0057  
**UPC Number:** 78621090967  
**EAN Number:** 05415022259155  
**Status:** A

1-1/2 Inch Straight Malleable Iron Insulated Liquidtight High Temperature Connector

- Sure-Tight gland deflects water away from connector and prevents "pooling" of moisture.
- Double beveled sealing ring designed with 5 unique sealing mechanisms and cannot be installed backwards
- Safe Edge ground cone provides superior bonding, stronger pullout, easy threading and conductor protection.
- Double plating for superior corrosion protection
- Heat Curled Insulator molded inside body provides excellent wire protection and easier glide of conductors through and into the fitting.

**North American Specifications (UNSPSC)**

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-Straight
Size	1-1/2 Inch
Material	Malleable Iron
Finish	Zinc Plating/Clear Chromate

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Surface protection	Zinc coated
Thread length	20.63mm
Total length	68.26mm
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	N
Operating temperature	0-+150°C

**Packaging**

Inner Quantity	2
Inner Dimensions (inches)	6.25x4.75x3.25
Outer Quantity	10
Outer Dimensions (inches)	21.62x5.12x6.62
Weight Uom	1.08 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000123
--------------------------------	-----------



Instruction Sheet	TA02544-TB2
Support/Tools	Available on Website
Catalog US	Available on Website
<b>Header</b>	
3D Model	Available on Website