



Actual



Representative

Catalog Number: 5337GR
Product ID: 7TAD012300R0010
UPC Number: 78621089626
EAN Number: 05414363143178
Status: A

2 Inch Steel External Bonding Liquidtight Insulated Connector Flexible Metal Conduit Fitting, Straight, With Copper Lug for Awg #4 to 2/0 Ground Wire, for Use In Wet Locations, 5 Pieces

- Ability to install quickly with low torque effort

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-Straight
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	2 Inch
Material	Steel
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Surface protection	Zinc coated
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Outer Quantity	5
Outer Dimensions (inches)	9.8x7x3.2
Weight Uom	198.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Support/Tools	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------

