



Representative

**Catalog Number:** 5338  
**Product ID:** 7TAD012190R0000  
**UPC Number:** 78621005338  
**EAN Number:** 05414363075691  
**Status:** A

2-1/2 Inch Straight Malleable Iron Insulated Liquidtight Connector

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

**North American Specifications (UNSPSC)**

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-Straight
Application	Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.
Standard	UL E23018, CSA
Size	2-1/2 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

**Packaging**

Outer Quantity	5
Outer Dimensions (inches)	12.5x8.5x4.12
Weight Uom	3.25 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000122
Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Catalog US	Available on Website

**Header**

3D Model	Available on Website
----------	----------------------

