



Actual



Representative

**Catalog Number:** 5340GR  
**Product ID:** 7TAD012300R0014  
**UPC Number:** 78621089629  
**EAN Number:** 05415022257687  
**Status:** A

4 Inch Steel External Bonding Liquidtight Insulated Connector Flexible Metal Conduit Fitting, Straight, With Copper Lug for Awg #2 to 4/0 Ground Wire, for Use In Wet Locations, 1 Piece

- Ability to install quickly with low torque effort

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-Straight
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	4 Inch
Material	Steel
Finish	Electro Zinc Plated/Chromate Coating

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

#### Packaging

Outer Quantity	1
Outer Dimensions (inches)	8.7x5.7x6.4
Weight Uom	772 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Support/Tools	Available on Website
Catalog US	Available on Website

#### Header

3D Model	Available on Website
----------	----------------------