



Representative

**Catalog Number:** 5342  
**Product ID:** 7TAD012130R0004  
**UPC Number:** 78621005342  
**EAN Number:** 05414363075714  
**Status:** A

1/2 Inch 45 Degree Malleable Iron Insulated Liquidtight Connector

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

**North American Specifications (UNSPSC)**

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-45 Degree
Application	Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.
Standard	UL E23018, CSA
Size	1/2 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

**Packaging**

Inner Quantity	25
Inner Dimensions (inches)	8x5x4
Outer Quantity	50
Outer Dimensions (inches)	8.49x5.19x8.13
Weight Uom	32.81 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000122
Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Catalog US	Available on Website

**Header**

3D Model	Available on Website
----------	----------------------

