



Representative

Catalog Number: 5342GR
Product ID: 7TAD012300R0016
UPC Number: 78621090003
EAN Number: 05415022257076
Status: A

1/2 Inch External Bonding Liquidtight Insulated Connector Flexible Metal Conduit Fitting, 45 Degree Angle, With Revolver Lug, With Tin to plated Copper Alloy Lug for Awg #14 to #2 Ground Wire, for Use In Wet Locations, 25 Pieces

- Ability to install quickly with low torque effort

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-45 degree
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	1/2 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel

Packaging

Inner Quantity	25
Inner Dimensions (inches)	9.5x6.5x4.5
Outer Quantity	50
Outer Dimensions (inches)	9.56x6.81x9.81
Weight Uom	35 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Catalog Page	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------