



Representative

**Catalog Number:** 5345GR  
**Product ID:** 7TAD012420R0075  
**UPC Number:** 78621090006  
**Status:** A

1-1/4 Inch 45 Degree Malleable Iron External Bonding Liquidtight Insulated Connector

- Ability to install quickly with low torque effort

**North American Specifications (UNSPSC)**

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-45 degree
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	1-1/4 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other

**Packaging**

Outer Quantity	5
Outer Dimensions (inches)	6.4x5.2x5.5
Weight Uom	1.25 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000120
Support/Tools	Available on Website
Catalog US	Available on Website

**Header**

3D Model	Available on Website
----------	----------------------