



Representative

Catalog Number: 5348GR
Product ID: 7TAD012420R0081
UPC Number: 78621089632
EAN Number: 05415022459425
Status: A

2-1/2 Inch 45 Degree Malleable Iron External Bonding Liquidtight Insulated Connector,

- Ability to install quickly with low torque effort

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-45 degree
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	2-1/2 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 1/2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other

Packaging

Outer Quantity	1
Outer Dimensions (inches)	8.5x6.5x4.19
Weight Uom	6.28 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Support/Tools	Available on Website
Catalog US	Available on Website

Header

3D Model	Available on Website
----------	----------------------