



Representative

**Catalog Number:** 5350GR  
**Product ID:** 7TAD012310R0035  
**UPC Number:** 78621089634  
**EAN Number:** 05415022459449  
**Status:** A

4 Inch 45 Degree Malleable Iron External Bonding Liquidtight Insulated Connector

- Ability to install quickly with low torque effort

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Grounding Connectors-45 degree
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	4 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	4 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	10.1x7x8.4
Weight Uom	1240 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Catalog Page	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

### Header

3D Model	Available on Website
----------	----------------------