



Actual

**Catalog Number:** 5352-PT  
**Product ID:** 7TAD012100R0053  
**UPC Number:** 78620969664  
**Status:** A

1/2 Inch 90 Degree Malleable Iron Insulated Liquidtight Push-in Connector

- High performance and pull-out strength
- Installs up to 3 times faster
- No disassembly required

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Connectors-90 Degree
Special Features	Innovative Labor-Saving Design, Simple Push-In Connection
Application	For Liquid and Dust-Tight Connections Between Flexible Jacketed Metallic Conduit and a Box or an Enclosure
Standard	UL E23018, CSA
Size	1/2 Inch
Material	Malleable Iron

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Plug-in connection
Thread type	NPT
Thread connection size	Other
One-piece	Y
Material housing	Other
Operating temperature	0-+105°C

#### Packaging

Inner Dimensions (inches)	xx
Outer Quantity	25
Outer Dimensions (inches)	6.5x4.75x5.25
Weight Uom	29 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000121
Instruction Sheet	TA04752-TB2
Support/Tools	Available on Website
Catalog US	Available on Website