



Actual



Representative

**Catalog Number:** 5358GR  
**Product ID:** 7TAD012420R0102  
**UPC Number:** 78621089637  
**Status:** A

2-1/2 Inch 90 Degree Malleable Iron External Bonding Liquidtight Insulated Connector

- Ability to install quickly with low torque effort

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Grounding Connectors-90 degree
Application	To positively bond conduit to box or enclosure
Standard	UL E3060, CSA
Size	2-1/2 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 1/2 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	12.8x10.5x5.2
Weight Uom	10 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000120
Catalog US	Available on Website

### Header

3D Model	Available on Website
----------	----------------------