



Actual

**Catalog Number:** 5360-SG  
**Product ID:** 7TAD012220R0002  
**UPC Number:** 78620992895  
**Status:** A

4 Inch 90 Degree Malleable Iron Insulated Connector With Sealing Gasket

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Liquidtight Insulated Connector
Size	4 Inch
Material	Iron

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	21.75x9.87x6.5
Weight Uom	2380 lbs. per 100