



Actual



Representative

Catalog Number: 5362
Product ID: 7TAD012260R0000
UPC Number: 78621005362
EAN Number: 05414363075837
Status: A

1/2 Inch Straight Steel Chase Liquidtight Insulated Connector With Electro-Zinc Plating

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Chase Connectors-Straight
Standard	UL E23018, CSA
Size	1/2 Inch
Material	Steel
Finish	Electro Zinc Plating

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Surface protection	Zinc coated
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x4.625x4
Outer Quantity	100
Outer Dimensions (inches)	9.5x8.875x7
Weight Uom	20.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
Catalog Page	Available on Website
Instruction Sheet	TA00210-TB2

Header

3D Model	Available on Website
----------	----------------------