



Actual



Representative

Catalog Number: 5368
Product ID: 7TAD012270R0004
UPC Number: 78621005368
EAN Number: 05414363100089
Status: A

2-1/2 Inch Straight Malleable Iron Chase Liquidtight Insulated Connector With Electro-Zinc Plating

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Liquidtight Flexible Metal Conduit Fittings
Special Features	UL Listed Liquidtight and CSA Certified Watertight
Standard	CSA, UL E23018
Size	2-1/2 Inch
Material	Malleable Iron - Insulated

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Surface protection	Zinc coated
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	1
Outer Quantity	5
Outer Dimensions (inches)	10.8x8.39x4.5
Weight Uom	4.02 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000122
Catalog Page	Available on Website
Instruction Sheet	TA00210-TB2

Header

3D Model	Available on Website
----------	----------------------