



Representative

**Catalog Number:** 5386  
**Product ID:** 7TAD012470R0007  
**UPC Number:** 78621005386  
**EAN Number:** 05414363143239  
**Status:** A

6 Inch Straight Malleable Iron Insulated Liquidtight Connector

- Ability to install quickly with low torque effort
- Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.
- To positively bond conduit to box or enclosure.

**North American Specifications (UNSPSC)**

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Liquidtight Flexible Metal Conduit Fittings
Special Features	UL Listed Liquidtight and CSA Certified Watertight
Size	6 Inch
Material	Malleable Iron - Insulated

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	Other
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	Y

**Packaging**

Outer Quantity	1
Outer Dimensions (inches)	9x9x9
Weight Uom	25 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000122
Instruction Sheet	TA00210-TB2
Support/Tools	Available on Website
Catalog US	Available on Website

**Header**

3D Model	Available on Website
----------	----------------------

