



Actual

Catalog Number: 5712
Product ID: 7TAD012560R0002
UPC Number: 78621005712
EAN Number: 05414363144724
Status: A

1 Inch Neoprene Liquidtight Knockout Plug

- Made of flame retardant neoprene, these new knockout plugs meet U.L. 514 flammability test.
- Provide a raintight, dust and oil-tight reusable seal for electrical knockouts.
- NEMA 3R, 4, 6 and 13 boxes can be saved or re-used whenever a knockout is no longer used.
- No tools needed to install; just push into hole and they snap in

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Knockout Plugs
Standard	UL E13938
Size	1 Inch
Material	Neoprene

European Specifications (ETIM)

ETIM	EC000032 Plug for cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 inch
Material	Plastic
Material quality	Other
Colour	Black

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x4.5x4
Outer Quantity	250
Outer Dimensions (inches)	21.44x9.5x6.31
Weight Uom	2 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------