



Actual

Catalog Number: 5715
Product ID: 7TAD012560R0005
UPC Number: 78621005715
EAN Number: 05414363144755
Status: A

2 Inch Neoprene Liquidtight Knockout Plug

- Made of flame retardant neoprene, these new knockout plugs meet U.L. 514 flammability test.
- Provide a raintight, dust and oil-tight reusable seal for electrical knockouts.
- NEMA 3R, 4, 6 and 13 boxes can be saved or re-used whenever a knockout is no longer used.
- No tools needed to install; just push into hole and they snap in

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Knockout Plugs
Standard	UL E13938
Size	2 Inch
Material	Neoprene

European Specifications (ETIM)

ETIM	EC000032 Plug for cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	2 inch
Material	Plastic
Material quality	Other
Colour	Black

Packaging

Outer Quantity	25
Outer Dimensions (inches)	8.9x4.8x6.9
Weight Uom	9.25 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------